


µDuct dielectric optical nano Flextube® cable

Cable Design

IEC/EN 60794



- not to scale -

Micro-module: Thin skin tubing (FlexTube®), filled with a suitable compound, housing the 200µm coated BendBright-XS optical fibres.

Water tightness: dry core with swellable elements.

Strength members: glass fibre reinforced plastic material.

Outer Sheath: HDPE.

This thin skin nano Flextube dielectric optical cable is designed for outdoor installation in µduct by jetting or floating technics. Mainly used in µduct for FTTx and access network.

This cable includes the PrysmianGroup BendBright-XS fibre with 200µm coating, providing the lowest attenuation at 1625nm after installation and splicing with miniaturized equipments thanks to its excellent behaviour against small bends.

The Flextube® design provides easier storage & faster installation.

Finger access to the fibres : no specific tools to open the Flextube.

One cable only will be installed in the same duct and the cable must be protected inside the manhole.

Technical data

# Fibres (grouped by 12)*	≤	12	48	72	96	144	288
Module - Ø	mm	1.2					
Cable Diameter	mm	4.0	5.4	6.0	6.3	7.2	9.4
Cable Weight	kg / km	10	20	25	30	35	50
Max installation tension	daN	20	40	50	60	70	100
Suggested duct inner dia.**	mm	6	8	8	10	10	12
Min. bending radius	mm	Without Tension 10 x Cable-Ø			Under Maximum Tension 20 x Cable-Ø		
Temperature range	°C	Installation -5 -> +40;		Transport. & Storage -40 -> +70 ;		Operation -30 -> +60	

* other configuration upon specific request.

** suggested optimized inner diameter for better air blowing performance

Please refer to our General Installation, Safety & Handling recommendations before handling.

Main characteristics

Test	Standard	Valeur	Sanction*
Maximum Tension at installation (short term)	IEC 60794-1-2-E1	see table above	Δα reversible
Crush	IEC 60794-1-2-E3	100 daN / 100mm	Δα reversible
Cable bend	IEC 60794-1-2-E11	R = 10 x cable Ø	Δα reversible
Temperature range	IEC 60794-1-2-F1	-30 -> +60°C	Δα ≤ 0.1 dB /km
Water Penetration	IEC 60794-1-2-F5B	sample=3m, water=1m	No water leakage after 24 hour

* values for single-mode fibres, all optical measurements performed at 1550 nm

Optical Characteristics

See the attached cabled optical fibre data sheet, BendBright-XS 200µm : C35

Provisional specification

Identification

Fibre Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	red	blue	green	yellow	violet	white	orange	grey	brown	black	aqua	pink

Flextube Colours for cables up to 144 fibres (≤ 12 modules)

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	red	blue	green	yellow	violet	white	orange	grey	brown	light green	aqua	pink

Flextube Colours for cables with more than 144 fibres (> 12 modules)

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	red	blue	green	yellow	violet	white	orange	grey	brown	light green	aqua	pink
No.	13	14	15	16	17	18	19	20	21	22	23	24
Colour	red	blue	green	yellow	violet	white	orange	grey	brown	light green	aqua	pink

Sheath Colour:

The outer sheath colour is black.

Sheath Marking:

The outer sheath is marked in 1 meter intervals as follows:

<Manufacturer> <year of manufacture> OPTICAL CABLE <optional: product type> <nb and type of fibre> <length marking in meter>

Logistic

Packing:

Wooden drums with protection.

Delivery Lengths:

Standard delivery length is 4 km with a tolerance of - 1% / + 3%

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.