

Properties of cable with BendBright® XS 200µm fibre

ESMF, low water peak G652D, OS2, G657A2&B2 low bend, FTTx

General and application

The optical fibres are made of a high grade doped silica core surrounded by a doped silica cladding; They are coated with a dual layer, UV cured acrylate based coating.

This enhanced low macro bending sensitive, low water peak fibre, gives unsurpassed bending performance. The preferred use of the BendBright® XS 200µm fibre is in high fibre count cables with small diameter specially installed in Fibre-to-the-Home networks. The BendBright® XS 200µm offers reduced bending radii for many cables types. The fibre fulfils the new ITU G.657 A2 and G.657 B2 specification (edition 2009), as well as G.652.D. The low macro bending sensitivity further guarantees that the 1625 nm window (L-band) will be available for future use in this bandwidth hungry environment

Standards and Norms

IEC 60793-2-50 Category B6_a and B6_b	EN 50 173-1:2007, cat. OS2
EN 60793-2-50: Class B6_a and B6_b	ISO/IEC 11801:2002, cat. OS2 and OS1
ITU Recommendation G.657.A2 and G.657.B2 (2009)	ISO/IEC 24702:2006 cat. OS2 and OS1
ITU Recommendation G.652 A, B, C and D (2009)	IEEE 802.3 – 2002 incl. 802.3ae

Optical properties

Attribute	Measurement method	Units	Limits
Mode field diameter at 1310 nm	IEC/EN 60793-1-45	µm	8.8 ± 0.4
Mode field diameter at 1550 nm		µm	9.8 ± 0.5
Chromatic dispersion coefficient:	IEC/EN 60793-1-42		
In the interval 1285 nm – 1330 nm		ps/km • nm	≤ 3.7
At 1550 nm		ps/km • nm	≤ 18.5
At 1625 nm	ps/km • nm	≤ 23.0	
Zero dispersion wavelength, λ ₀		nm	1300 - 1324
Zero dispersion slope		ps/(nm ² • km)	≤ 0.092
Cut-off wavelength	IEC/EN 60793-1-44	λ _{cc} nm	≤ 1260 *
Polarisation mode dispersion (PMD) coefficient	IEC/EN 60793-1-48	ps/√km	≤ 0.1
PMD _Q Link Design Value (computed with Q=0.01%, N=20)	IEC/EN 60794-3	ps/√km	≤ 0.06

* guaranteed value according to the ITU-T (ATM G650) method

Attenuation

Attribute	Measurement method	Units	Limits
Maximum attenuation value of cable at 1310 nm	IEC/EN 60793-1-40	dB/km	≤ 0.38
Maximum attenuation value of cable at 1383 nm*	IEC/EN 60793-1-40	dB/km	≤ 0.38
Maximum attenuation value of cable at 1550 nm	IEC/EN 60793-1-40	dB/km	≤ 0.23
Maximum attenuation value of cable at 1625 nm	IEC/EN 60793-1-40	dB/km	≤ 0.25
Local discontinuity at 1310 and 1550 nm	IEC/EN 60793-1-40	dB	max. 0.1

* Including H2-ageing according to IEC 60793-2-50, type B.1.3, @1383nm

Attenuation variation vs Bending

Attribute	Measurement method	Units	Limits
10 turns on a mandrel R = 15 mm, @1550nm	IEC/EN 60793-1-47	dB	≤ 0.03
10 turns on a mandrel R = 15 mm, @1625nm	IEC/EN 60793-1-47	dB	≤ 0.1
1 turn on a mandrel R = 10 mm, @1550nm	IEC/EN 60793-1-47	dB	≤ 0.1
1 turn on a mandrel R = 10 mm, @1625nm	IEC/EN 60793-1-47	dB	≤ 0.2
1 turn on a mandrel R = 7.5 mm, @1550nm	IEC/EN 60793-1-47	dB	≤ 0.5
1 turn on a mandrel R = 7.5 mm, @1625nm	IEC/EN 60793-1-47	dB	≤ 1.0

Group index of refraction

Attribute	Measurement method	Units	Values
1310 nm	IEC/EN 60793-1-22	-	1.467
1550 nm	IEC/EN 60793-1-22	-	1.467
1625 nm	IEC/EN 60793-1-22	-	1.468

Geometrical properties

Attribute	Measurement method	Units	Limits
Cladding diameter	IEC/EN 60793-1-20	µm	125.0 ± 0.7
Cladding non-circularity	IEC/EN 60793-1-20	%	≤ 0.7
Core (MDF) -cladding concentricity error	IEC/EN 60793-1-20	µm	≤ 0.5
Primary coating diameter – ColorLock ^{XS} and natural	IEC/EN 60793-1-21	µm	200 ± 10
Primary coating non-circularity	IEC/EN 60793-1-21	%	≤ 5
Primary coating-cladding concentricity error	IEC/EN 60793-1-21	µm	≤ 10

Mechanical properties

Attribute	Measurement method	Units	Limits
Proof stress level	IEC/EN 60793-1-30	GPa	≥ 0.7 (≈ 1 %)
Strip force (peak)	IEC/EN 60793-1-32	N	1.0 ≤ F _{peak.strip} ≤ 8.9
Dynamic fatigue resistance aged and unaged	IEC / EN 60793-1-33	(N _d)	≥ 20
Static fatigue, aged	IEC / EN 60793-1-33	(N _s)	≥ 23

All measurements in accordance with ITU-T G650 recommendations

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup.