

C12: MaxCap-OM3 multimode fibre

Properties for cabled MaxCap-OM3 fibre

General and application

This cabled fibre is a graded-index multimode fibre optimised for 10 Gb/s transmission speeds. It has a 50 µm core diameter and a 125 µm cladding diameter. The fibre is designed for use at 850 nm, but can also be used at 1300 nm. The fibre is compliant with all relevant network standards. This fibre was formerly named MaxCap 300

Standards

IEC 60793-2-10: type A1a.2	EN 50 173:2002 category OM3
EN 60793-2-10: type A1a.2	ISO/IEC 11801:2002 category OM3
TIA/EIA-492 AAAC	IEEE 802.3 - 2002 incl. amendment 802.3ae - 2002.

Optical properties

<i>Attribute</i>	<i>Measurement method</i>	<i>Units</i>	<i>Limits</i>
Attenuation limit according to IEC 60793-2-10, 850 nm	IEC 60793-1-40	dB/km	≤ 2.5
Attenuation limit according to IEC 60793-2-10, 1300 nm	IEC 60793-1-40	dB/km	≤ 0.8
Inhomogeneity of OTDR trace for any two 1000 metre fibre lengths	IEC 60793-1-40	dB/km	Max. 0.1
Numerical aperture	IEC 60793-1-43	-	0.200 ± 0.015

Cable attenuation

Maximum attenuation value of cable at 850 nm	IEC 60793-1-40	dB/km	≤ 3.0
Maximum attenuation value of cable at 1300 nm	IEC 60793-1-40	dB/km	≤ 1.0

Bandwidth

Overfilled (OFL) modal bandwidth at 850 nm	IEC 60793-1-41	MHz • km	≥ 1500
Overfilled (OFL) modal bandwidth at 1300 nm	IEC 60793-1-41	MHz • km	≥ 500
Effective Modal Bandwidth (EMB) at 850 nm	IEC 60793-1-49	MHz • km	≥ 2000

Group index of refraction

Group index of refraction at 850 nm	IEC 60793-1-22	-	1.482
Group index of refraction at 1300 nm	IEC 60793-1-22	-	1.477

C12: MaxCap-OM3 multimode fibre

Geometrical properties

Attribute	Measurement method	Units	Limits
Core diameter	IEC 60793-1-20	µm	50 ± 2
Cladding diameter	IEC 60793-1-20	µm	125.0 ± 1.0
Cladding non-circularity	IEC 60793-1-20	%	≤ 0.7
Core non-circularity	IEC 60793-1-20	%	≤ 5
Core-cladding concentricity error	IEC 60793-1-20	µm	≤ 1
Primary coating diameter – uncoloured	IEC 60793-1-21	µm	242 ± 5
Primary coating diameter - coloured	IEC 60793-1-21	µm	250 ± 15
Primary coating non-circularity	IEC 60793-1-21	%	≤ 5
Primary coating-cladding concentricity error	IEC 60793-1-21	µm	≤ 6

Mechanical properties

Attribute	Measurement method	Units	Limits
Proof stress level	IEC 60793-1-30	GPa	≥ 0.7 (≈ 1 %)
Typical average strip force	IEC 60793-1-32	N	1.7
Strip force (peak)	IEC 60793-1-32	N	$1.3 \leq F_{\text{peak.strip}} \leq 8.9$

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.