


# UC900 SS23 Cat.7 LSH-FR C<sub>ca</sub> s1d1a1

**S/FTP AWG23/1**



## Einsatzgebiete

Primär (Campus), Sekundär (Riser), Tertiär (Horizontal)  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; **10GBase-T**  
IEEE 802.5 16 MB; ISDN; TPDDI; ATM  
Power over Ethernet (PoE) / Type 1-4

## Geltende Normen

EN 50173-1; EN 50288-4-1  
ISO/IEC 11801; IEC 61156-5  
IEEE 802.3af / at / bt

## Flammwidrigkeit

EN 50399: Class C<sub>ca</sub>s1d1a1  
LSHF-FR (LSOH-FR): IEC 60332-1; IEC 60332-3-24; IEC 60754-2; IEC 61034

## Kabelaufbau

Leiter	Cu-Draht, blank Ø 0,56 mm (AWG 23/1)
Isolierung	Foam-Skin Polyethylen, Ø 1,38 mm
Verseilung	2 Adern zum Paar
Paarabschirmung	Aluminium-beschichtete Kunststoff-Verbundfolie
Verseilung zur Seele	4 Paare (PiMF) zur Seele
Gesamtabschirmung	Cu-Geflecht verzinkt
Schutzmantel	LSHF-FR C <sub>ca</sub> , orange RAL 2003

## Mechanische Eigenschaften

Biegeradien	ohne Zugbelastung	4 x D
	mit Zugbelastung	8 x D
Betriebstemperaturbereich	ruhend	-20°C bis + 60°C
	bewegt	0°C bis + 50°C

# UC900 SS23 Cat.7 LSH-FR C<sub>ca</sub> s1d1a1

## Elektrische Eigenschaften

bei 20°C ± 5°C

Schleifenwiderstand		154 Ω/km	
Widerstandsunsymmetrie		≤ 2%	
Isolationswiderstand	(500 V)	≥ 5000 MΩ *km	
Kapazität	bei 800 Hz	Nom. 43 nF/km	
Kapazitätsunsymmetrie	(Paar/Erde)	≤ 1500 pF/km	
Mittlerer Wellenwiderstand	100 MHz	100 ± 5 Ω	
Relative Ausbreitungsgeschwindigkeit		ca. 79 %	
Signallaufzeit		≤ 425 ns/100m	
Laufzeitunterschied		≤ 9 ns/100m	
Prüfspannung	(DC, 1 min) Ader/Ader und Ader/Schirm	1000 V	
Kopplungswiderstand	bei 1 MHz	5 mΩ /m	Grade 1
	bei 10 MHz	5 mΩ /m	
	bei 30 MHz	10 mΩ /m	
Kopplungsdämpfung		85 dB	Type 1
Trennklasse gem. EN 50174-2			„D“

## Elektrische Daten (nominal)

gem. Cat.7 (bei 20°C)

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ACRF (dB/100m)	PS-ACRF (dB/100m)	Return loss (dB)
1,0	1,8	104	101	102	99	105	105	-
4,0	3,4	100	97	97	94	105	102	27
10,0	5,4	100	97	95	92	97	94	30
16,0	6,8	100	97	93	90	93	90	30
20,0	7,7	100	97	92	89	91	88	30
31,2	9,6	100	97	90	87	87	84	30
62,5	13,7	100	97	86	83	81	78	30
100,0	17,4	100	97	83	80	77	74	30
125,0	19,5	95	92	75	72	75	72	26
155,5	21,9	94	91	72	69	73	70	26
175,0	23,3	93	90	70	67	72	69	25
200,0	25,0	92	89	67	64	71	68	25
250,0	28,1	90	87	62	59	69	66	24
300,0	30,9	89	86	58	55	67	64	24
450,0	38,3	87	84	48	45	64	61	23
600,0	44,8	85	82	40	37	61	58	22
750,0	52,0	83	80	31	28	59	56	21
900,0	59,4	82	79	23	20	58	55	20
1000,0	63,1	80	77	17	14	57	54	20

## UC900 SS23 Cat.7 LSH-FR C<sub>ca</sub> s1d1a1

### Technische Angebotsdaten

Artikelnummer/ Referenz Code	Kurzbezeichnung	Produktname	Außendurchmesser  mm	Euro class	Brandlast		Gewicht  kg/km	Cu-Zahl	Zugkraft  N
					MJ/km	kWh/m			
tbd. 60060629	J-02YSCH 4x2x0,56 PiMF	UC900 SS23 Cat.7 LSHF-FR C <sub>ca</sub> s1d1a1	7.3	C <sub>ca</sub> s1d1a1	580	0,16	65	38	180
60065309		UC900 SS23 Cat.7 LSHF-FR C <sub>ca</sub> s1d1a1 1000DW							
60065310	J-02YSCH 2x4x2x0,56 PiMF	UC900 SS23 C7 S/FTP 2x4P LSFR C <sub>ca</sub>	7.5 x 15.2	C <sub>ca</sub> s1d1a1	1180	0,33	125	76	320
60065310		UC900 SS23 C7 S/FTP 2x4P LSFR C <sub>ca</sub> 500DW							

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.